

Technical data sheet 4S00

Specification Four legs, stackable

Dimensions in mm	Backrest:	H:	470
		Seat:	H: 440
	Total:	W:	450
		D:	470
		H:	890
		W (no ArmR):	495
Packaging data	Weight:	kg	8,30
		Volume:	m³ 0,40
	W (ArmR):	kg	8,30
		D:	470



Basic equipment

Benefit

Backrest	Seat and back upholstered, breath actively form foam, CFC - CHC - free (segregated foam). Seat 35 mm and back 25 mm.	Paddings are unglued, ensuring optimal air movement, breathable. Good sitting comfort.
Frame	Four leg frame, powder coated black with polyamide glides. Stackable.	Very high stability, longevity. Coating against scratches, etc.
Seat carrier	Moulded wood, serves at the same time as upholstery carrier.	
Plastic parts	Always black, dyed. Thus "colourfast" also with deep scratches and scars.	Very hard wearing.
Materials	All materials are segregated and recyclable.	Environmentally friendly.
Standards	DIN 16139 four leg and cantilever. GS-Symobl for tested safety, tested for contaminants, Ergonomics approved.	High safety.
Certification	Quality management system DIN EN ISO 9001:2008, VO (EG) No. 1221/2009 (EMAS), Environmental management system DIN EN ISO 14001:2009, OHSAS, EcoVadis gold, Commitment to sustainability. Quality Office, Blue Angel. Bifma e3 level Platin.	High- quality product.
Warranty and return	10 years warranty. Complete return and recycling guarantee.	Exchange of parts free of charge, within the guaranteed period.

Disassembly instructions are available upon request for any interstuhl product

Technical data sheet 4S00

Specification Four legs, stackable

Dimensions in mm	Backrest:	H:	470	
		Seat:	H:	440
			W:	450
			D:	470
	Total:	H:	890	
		W (no ArmR):	495	
W (ArmR):		580		
D:		470		
Packaging data	Weight:	kg	8,30	
	Volume:	m ³	0,40	



Options			Benefit
Upholstery materials	Various fabric and leather options available.		Individual design.
Frame	Four leg frame made of tubular steel, chromed.		Very high stability, longevity. High-quality look.
Glides	Felt glides for hard floors.		Optimal positioning of the chair. Saves the floor.

Disassembly instructions are available upon request for any interstuhl product