

Technical data sheet 862S

Specification Lectern, 650 x 650 mm

Dimensions in mm

Total:	H:	720-1015
	W:	650
	D:	650



Packaging data	Weight:	kg	13,5
	Volume:	m³	0,45

Basic equipment

Benefit

Standing frame	Aluminium base, 4 legs. Height adjustable column adjusted by bowden cable (2 castors, 2 glides).	Very good stability.
Metal parts, colour finish	Powder-coated black or white.	Attractive look.
Glides/Castors	Hard for soft floors.	Optimum stability.
Table top	HPL white, 26 mm. Edges: 6 mm straight, 20 mm bevelled edge.	Bevelling the top edge gives the table a more stylistic appearance.
Certification	Quality management system DIN EN ISO 9001:2015, Regulation (EC) no. 1221/2009 (EMAS), Environmental Management System DIN EN ISO 14001:2015, Occupational Health and Safety Management System DIN EN ISO 45001:2018, Energy management system DIN EN ISO 50001:2018, EcoVadis Gold, Commitment to sustainability.	High-quality product.
Warranty	10 year warranty according to our current warranty conditions.	Quality guaranteed to last for entire product life.

Disassembly instructions are available upon request for any interstuhl product

Technical data sheet 862S

Specification Lectern, 650 x 650 mm

Dimensions in mm

Total:	H:	720-1015
	W:	650
	D:	650



Packaging data	Weight:	kg	13,5
	Volume:	m³	0,45

Options

Benefit

Metal parts, colour finish Brushed, silver.

Brushing is a method that emphasise the character and material properties of aluminium in a particularly genuine way. This also includes minor irregularities in the surface that make every chair/table a unique item. A subsequently applied protecting lacquer prevents premature signs of ageing; on the other hand, aluminium is a material that tends to become more valuable the more its is used.

Table top finishes Oak, American walnut, European cherry, Makassar or Minerale cocoon (acrylate-bonded natural mineral) white, 26 mm. Edges: 6 mm straight, 20 mm bevelled edge.

Individual design.

Glides/Castors Soft for hard floors.

Optimum stability, spare the floor.

Disassembly instructions are available upon request for any interstuhl product